## Formulating a Greener World®

# HydraJET® 2030R

Aqueous ink for semi-porous media













#### **TECHNICAL DATA SHEET**

HydraJET® 2030R red aqueous TIJ 2.5 ink consists of FDA approved FD&C dyes. HydraJET® 2030R ink provides eye-catching color, crisp and sharp text, logo and barcode, and fast drying time on semi-porous substrates.

#### **Technical Specifications**

	HydraJET® 2030R Print Cartridge
Ink type	Red dye aqueous ink
Print cartridge type	HP 45ai
Resolution	Up to 600 dpi, recommended $300 \times 300$ dpi
Nozzle count	300
Print swath	12.7 mm
Firing voltage	11.0 V
Fire pulse width	1.8 μs
Pulse warming	OFF
Decap time	1 h
Drying time	$1 - 3 \text{ s}$ at $300 \times 300 \text{ dpi}$
Throw distance	Up to 3 mm
Average delivered ink	40 mL (vertical)
Average drop volume	27 pL
Operating conditions	15 °C to 35 °C, 35% to 80% RH
Shipping / storage temperature	10 °C to 35 °C
Best before	12 months from filling date

#### Cartridge Shipping & Storage

- Store the cartridge with a clip placed over the printhead. Nozzles up or horizontal.
- Refer to Safety Data Sheet for more information.

### Cartridge Maintenance & Handling

- Use a lint-free cloth moistened with deionized water to clean the cartridge printhead.
- Holding the cartridge printhead face down, gently press the printhead on a lint-free cloth to allow ink to wick out. Then, slowly and lightly wipe across the tip of the long edge.
- Do not shake the cartridge.

#### **Ordering Information**

Product number	Product description
2030R42A	HydraJET® 2030R Print Cartridge

#### **MYLAN GROUP**

Longduc Industrial Park, Travinh City, Travinh Province, Vietnam

Tel.: +84 294 3846 997 - Fax: +84 294 3846 998 Email: info@mylangroup.com

Website: www.mylangroup.com